



gentec-e)

QE12HR-H-MB-D0

Pyroelectric detector for laser energy measurement up to 0.85 J.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

0.7 µJ for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read mo

HIGH REPETITION RATE OPTIONS

- QE12HR-MB: 1 000 Hz
- QE12HR-MT: 10 000 Hz

TEST TARGET INCLUDED

With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-D-233

SPECIFICATIONS

Spectral range ¹	0.193 - 20 µm
Typical rise time	70 µs
Repeatability	<0.5%
Maximum repetition frequency ²	1000 Hz
Maximum measurable energy ³	0.85 J
Noise equivalent energy ⁴	1.4 µJ
Maximum pulse width	40 µs
Energy calibration uncertainty	±3 %

nergy 4. Nominal value. Actual value depends on electrical noise in the measurement system.

DAMAGE THRESHOLDS

Maximum average power density ¹	10 W/cm ²
Maximum energy density ²	0.6 J/cm ²
Maximum power	5 W
1. May vary with wavelength and average power.	

2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS

Coo	lina

Cooling	Convection (heatsink)
Aperture width	12 mm
Aperture height	12 mm
Absorber	МВ
Dimensions	36H x 36W x 33D mm





203895 203903

205363

ORDERING INFORMATION

QE12HR-H-MB-D0

QE12HR-H-MB-INT-D0

QE12HR-H-MB-INE-D0

QE12HR-H-MB-IDR-D0

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us