





High Frequency Charge Amplifier

Specifications	Test conditions	$V_{\text{S}}=\pm15$ V, $T_{\text{A}}=25$ °C, output load impedance 1 M $\Omega,$ warm-up 20 minutes (min. 10 minutes recommended)
Gain	Charge gain Gain accuracy Equivalent current gain	10 V/pC (@ output load ≥ 100 kΩ) ±3 % 1.6 V/µA (@ 1 MHz sinusoidal input signal, output load ≥ 100 kΩ)
Frequency Response	Lower cut-off frequency (–3 dB) Upper cut-off frequency (–3 dB)	250 Hz 15 MHz typ. (with max. 100 pF source capacitance)
Input	Input impedance Effective AC input impedance Input charge noise Equivalent input current noise Input voltage noise Max. input charge	1 GΩ II 10 nF 20 Ω (@ 1 MHz) 40 × 10 ⁻²¹ C/√Hz (@ 1 MHz, open input) 90 × 10 ⁻²¹ C/√Hz (@ 1 MHz, 100 pF source capacitance) 250 fA/√Hz (@ 1 MHz, open input) 570 fA/√Hz (@ 1 MHz, 100 pF source capacitance) 700 pV/√Hz (@ 1 MHz) 1 pC _{PP}
Output	Output voltage range Output impedance Max. output current Output noise	10 V _{PP} (@ \geq 100 k Ω output load, for linear operation) 5 V _{PP} (@ 50 Ω output load) 50 Ω (for best performance terminate with \geq 100 k Ω load) 100 mA (short-circuit proof) 1.5 mV _{RMS} (10 mV _{PP}) typ. (@ open input) 4.6 mV _{RMS} (30 mV _{PP}) typ. (@ 100 pF source capacitance) (@ \geq 1 M Ω load, measuring bandwidth 200 MHz)
Power Supply	Supply voltage Supply current	± 15 V (± 14.5 V ± 16.5 V) ± 35 mA (depends on operating conditions, recommended power supply capability min. ± 100 mA)
Case	Weight	200 g (0.44 lbs) Material AIMg4.5Mn, nickel-plated
Temperature Range	Storage temperature Operating temperature	-40 °C +85 °C 0 °C +40 °C
Absolute Maximum Ratings	Input voltage Power supply voltage	20 V _{PP} ±18 V
Connectors	Input Output Power supply	BNC jack (female) BNC jack (female) LEMO® series 1S, 3-pin fixed socket (mating plug type: FFA.1S.303.CLAC52) PIN 2 -Vs Pin 1: +15 V Pin 2: -15 V Pin 3: GND
Scope of Delivery	HQA-15M-10T, LEMO [®] 3-pin connector, datasheet, transport package	
Ordering Information	HQA-15M-10T	High frequency charge amplifier
SOPHISTICATED TOOLS FOR SIGNAL RECOVERY		





HQA-15M-10T Datasheet **High Frequency Charge Amplifier** Operation The amplifier is AC coupled for direct use with a charge sensor producing sinusoidal signals with no DC background. A source capacitance of less than 1 nF is recommended for proper operation. If the effective source capacitance (sensor plus cable capacitance) is small relative to the effective input impedance of the amplifier (10 nF) the amplifier acts as a virtual ground and most of the charge flows into the amplifier input. At 1 MHz the amplifier input capacitance of 10 nF corresponds to a complex input impedance of 20 Ω . An input resistor of 1 G Ω is incorporated to prevent buildup of static charge. The amplifier is not suited for sources producing an average DC background current as this would saturate the device. Dimensions HQA-15M-10T 94 87 74 0 Ο OUT IN BW 250 Hz - 15 MHz 44 5 10 V/pC Galn HQA-15M-10T Е ⋗ т \cap \cap Ø 3.2 ഹ 0 80. DZ01-299001 R6 all dimensions are in mm unless otherwise noted FEMTO Messtechnik GmbH Specifications are subject to change without notice. Information provided herein is believed to be accurate and Klosterstr. 64 reliable. However, no responsibility is assumed by FEMTO Messtechnik GmbH for its use, nor for any infringement 10179 Berlin · Germany of patents or other rights of third parties which may result from its use. No license is granted by implication or Phone: +49 30 280 4711-0 otherwise under any patent or patent rights of FEMTO Messtechnik GmbH. Product names mentioned may also be Fax: +49 30 280 4711-11 trademarks used here for identification purposes only. Email: info@femto.de © by FEMTO Messtechnik GmbH · Printed in Germany www.femto.de Ο SOPHISTICATED TOOLS FOR SIGNAL RECOVERY